

辅助物镜

■ 适用于数码显微镜

5303-AF103, 5310-DL401,
5315-S710, ISM-DL300,
ISM-DL301, ISM-DL510,
ISM-DL400, ISM-DL500,
5317-AF110, 5317-AF109,



0.3X辅助物镜*
ISM-DL-OB03X



0.5X辅助物镜*
ISM-DL-OB05X



0.75X辅助物镜*
ISM-DL-OB075X



1X辅助物镜
ISM-DL-OB1X



1.5X辅助物镜
ISM-DL-OB1D5X



2X辅助物镜
ISM-DL-OB2X

放大倍率、焦距和视场(5303-AF103)

辅助物镜	技术参数	相机接口	
		0.5X(标配)	1X(选配)
0.3X (选配)	放大倍率	6~37X	12~74X
	焦距	120~310mm	120~310mm
	视场	52×30~8×5mm	26×15~4×2.5mm
0.5X (选配)	放大倍率	10~61X	20~123X
	焦距	78~230mm	78~230mm
	视场	37×20~5×3mm	18×10~2.5×1.5mm
0.75X (选配)	放大倍率	15~92X	30~184X
	焦距	60~125mm	60~125mm
	视场	21×13~3.4×2mm	10×6.5~1.7×1mm
1X (标配)	放大倍率	20~123X	40~246X
	焦距	48~84mm	48~84mm
	视场	15×8~2.5×1.5mm	7.5×4~1.3×0.7mm
1.5X (选配)	放大倍率	30~184X	60~368X
	焦距	36~63mm	36~63mm
	视场	10×6~1.7×1mm	5×3~0.9×0.5mm
2X (选配)	放大倍率	40~246X	80~492X
	焦距	24~42mm	24~42mm
	视场	7.5×4~1.3×0.7mm	3.8×2~0.7×0.4mm

放大倍率、焦距和视场(ISM-DL300, ISM-DL301, ISM-DL510)

辅助物镜	技术参数	相机接口	
		0.5X(标配)	1X(选配)
0.3X (选配)	放大倍率	5~34X	10~68X
	焦距	287±2mm	287±2mm
	视场	42×26~6.5×4.5mm	21×13~3.3×2.3mm
0.5X (选配)	放大倍率	9~56X	18~112X
	焦距	166±2mm	166±2mm
	视场	25.6×16.8~4×2.6mm	12.8×8.4~2×1.3mm
0.75X (选配)	放大倍率	13~84X	26~168X
	焦距	105±2mm	105±2mm
	视场	17×10.5~2.6×1.7mm	8.5×5.3~1.3×0.9mm
1X (标配)	放大倍率	15~100X	30~200X
	焦距	70±2mm	70±2mm
	视场	16×11~2.5×1.6mm	7.8×5.3~1.2×0.8mm
1.5X (选配)	放大倍率	26~168X	52~336X
	焦距	42±2mm	42±2mm
	视场	8.5×5.2~1.3×0.9mm	4.3×2.6~0.7×0.5mm
2X (选配)	放大倍率	30~200X	60~400X
	焦距	29±2mm	29±2mm
	视场	7.8×5.3~1.2×0.8mm	3.8×2.7~0.6×0.4mm

*如使用0.3X, 0.5X, 0.75X辅助物镜, 需要使用ISM-DL301, ISM-DL400, ISM-DL500, ISM-DL510, 5310-DL401底光源或LED辅助照明
(型号ISM-DL-LED)